



Article Number: 1.61.002

Product Range

Safety equipment

Product Category

Dim.: appr. 1270 x 870 x 400 (W x D x H in mm),
collection volume: 225 l

load bearing capacity: 900 kg

low tare weight: 62 kg

plastic structure made from extruded
laminate (PE-HD),

with stable PE perforated plate as standing level
accessible due to 100 mm base design.

suitable for water polluting,
non-flammable liquids WGK 1-3,

Tested:

General national technical approval of
DIBT-Berlin, MPA-tested, TÜV-tested

HW-category	Collecting trays
HW product filter	polyethylene
Outer width approx.	870 mm
Outer depth approx.	1270 mm
Outer height approx.	400 mm
Weight (product) approx.	64 kg