



Article Number: 11.90.910

Product Range

Safety equipment

Product Category

Fine granulate made from thermoset polymers,
can be used for all liquids,
absorbs up to 75 times its own weight,
economical and problem-free measure,
does not trigger any dangerous reactions.
also usable in rain, (ph-neutral)
Indicates the binder's saturation by dry deposit
on the surface.

Barrier formation possible, swells,
has an indicator function - Indicator transition:
acids (yellow) / lyes (red)

Testings:

Tested and approved by MPA NRW, Dortmund
and also tested by the Hygiene Institute
in Gelsenkirchen.

Retail category	Emergency products
Retail product filter	Absorber and binders
Outer width	8 mm
Outer depth	12 mm
Outer height	23 mm
Weight (product)	0,865 kg