



Article Number: 11.90.930

Product Range

Safety equipment

Product Category

Fine granulate made from thermoset polymers,
can be used for all liquids,
absorbs up to 75 times its own weight,
economical and problem-free measure,
does not trigger any dangerous reactions.

also usable in rain, (ph-neutral)

Indicates the binder's saturation by dry deposit
on the surface.

Barrier formation possible, swells,

has an indicator function - Indicator transition:

acids (yellow) / lyes (red)

Testings:

Tested and approved by MPA NRW, Dortmund

and also tested by the Hygiene Institut

in Gelsenkirchen.

Retail category	Emergency products
Retail product filter	Absorber and binders
Outer width	24 mm
Outer depth	39 mm
Outer height	20 mm
Weight (product)	5,6 kg