



filter unit line

Article Number: 2.00.398

Product Range

Safety equipment

Product Category

HW-category	Monitoring
Line	filter unit
HW product filter	Filter systems
CE conformity	Yes

Technical specifications

Outer width approx.	460 mm
Outer depth approx.	415 mm
Outer height approx.	325 mm
Power supply	230V - 50Hz - IEC 61439
Weight (product) approx.	18 kg
Connector Type	Type E+F: CEE 7/7
Potential-free contact	Yes
Exhaust air monitoring	Yes

Safety Equipment-General

Material of product	Sheet steel
Colour of product	Silver with pearlescent effect
Display	yes - LED
Activated Carbon Filter	yes - interchangeable
Filter Medium	according to substance list
Particle Filter	yes - interchangeable
Power of Activated Carbon Filter	30% of the filling quantity of the specified media

Safety Equipment-Certification

ATEX-Conformity	CE Ex II (3) G [n T4]
Low Voltage Directive 2006/95/EG	yes
PTB approval	yes - no. 14 ATEX D027
Noise Level	low noise

Safety Equipment-Monitoring

Monitoring of Filter	yes - changing intervall
Alarm	yes - visual and acoustic
IoT connectivity	radio - BT

Safety Equipment-Accessories

Product Accessories	2.00.393
---------------------	----------