



## UTS line

Article Number: 29-061159-005

**Product Range**

Safety storage cabinet

**Product Category**

Type 90 - flammable liquids

## General

|                            |                 |
|----------------------------|-----------------|
| <b>Line</b>                | UTS             |
| <b>Version</b>             | pro             |
| <b>Size</b>                | LD-5            |
| <b>Type</b>                | 90              |
| <b>Storage type</b>        | passive storage |
| <b>Functionality</b>       | Storage         |
| <b>Earthing connection</b> | Yes             |
| <b>Connection socket</b>   | Yes             |

## Test criteria and documentation

|  |                 |
|--|-----------------|
| <b>TÜV Süd certificate no.</b>         | Z1A 012906 0521 |
| <b>TÜV-Süd certificate type</b>        | GS              |
| <b>TÜV-Süd High Quality Zertifikat</b> | Z2 012906 0513  |
| <b>DIN EN 14470-1</b>                  | Yes             |
| <b>DIN EN 16121/16122</b>              | Yes             |
| <b>CE conformity</b>                   | Yes             |

## Technical specifications

|  |         |
|--|---------|
| <b>Outer width approx.</b>                         | 1100 mm |
| <b>Outer depth approx.</b>                         | 494 mm  |
| <b>Outer height approx.</b>                        | 631 mm  |
| <b>Max. load bearing capacity per storage area</b> | 40 kg   |
| <b>Max. load</b>                                   | 80 kg   |
| <b>Max. total weight</b>                           | 250 kg  |
| <b>Max. volume of single container left side</b>   | 7 L     |
| <b>Max. volume of single container right side</b>  | 7 L     |
| <b>Collection volume left side</b>                 | 8,4 L   |
| <b>Collection volume right side</b>                | 8,4 L   |
| <b>Weight (product) approx.</b>                    | 170 kg  |

## Cabinet

|                                     |              |
|-------------------------------------|--------------|
| <b>Material of cabinet cladding</b> | Sheet steel  |
| <b>Cabinet colour</b>               | RAL 7035     |
| <b>Material of inner lining</b>     | Decor panels |
| <b>Colour of inner lining</b>       | RAL 7035     |
| <b>Base</b>                         | Classical    |
| <b>Base height approx.</b>          | 35 mm        |
| <b>Base colour</b>                  | RAL 7015     |

## Doors

|                               |               |
|-------------------------------|---------------|
| <b>No. of doors</b>           | 2             |
| <b>Kind of door</b>           | Wing door     |
| <b>Material of door cover</b> | Sheet steel   |
| <b>Door colour</b>            | RAL 1018      |
| <b>Door operation</b>         | Classical     |
| <b>Door technology</b>        | Push-to-open  |
| <b>Lock</b>                   | Cylinder lock |
| <b>Locking system</b>         | Open          |
| <b>Locking points</b>         | 1-point       |

## Interior fittings

|                                      |                         |
|--------------------------------------|-------------------------|
| <b>Material of interior fittings</b> | Sheet steel             |
| <b>Colour of interior fittings</b>   | RAL 7035                |
| <b>Centre partition wall</b>         | Yes                     |
| <b>Bottom tray</b>                   | Extendable              |
| <b>Bottom tray insert</b>            | Perforated sheet insert |
| <b>Storage levels</b>                | 1                       |
| <b>Storage areas</b>                 | 2                       |
| <b>setting height approx.</b>        | 340 mm                  |