



## PREMIUM line

Article Number: 29-200662-051

**Product Range**

Safety storage cabinet

**Product Category**

Type 90 - flammable liquids

## General

|                            |                 |
|----------------------------|-----------------|
| <b>Line</b>                | PREMIUM         |
| <b>Version</b>             | pro             |
| <b>Size</b>                | M               |
| <b>Type</b>                | 90              |
| <b>Storage type</b>        | passive storage |
| <b>Functionality</b>       | Storage         |
| <b>Earthing connection</b> | Yes             |
| <b>Connection socket</b>   | Yes             |

## Test criteria and documentation

|  |                 |
|--|-----------------|
| <b>TÜV Süd certificate no.</b>         | Z1A 012906 0518 |
| <b>TÜV-Süd certificate type</b>        | GS              |
| <b>TÜV-Süd High Quality Zertifikat</b> | Z2 012906 0513  |
| <b>DIN EN 14470-1</b>                  | Yes             |
| <b>DIN EN 16121/16122</b>              | Yes             |
| <b>CE conformity</b>                   | Yes             |

## Technical specifications

|  |         |
|--|---------|
| <b>Outer width approx.</b>                         | 594 mm  |
| <b>Outer depth approx.</b>                         | 597 mm  |
| <b>Outer height approx.</b>                        | 2037 mm |
| <b>Max. load bearing capacity per storage area</b> | 40 kg   |
| <b>Max. load</b>                                   | 240 kg  |
| <b>Max. total weight</b>                           | 565 kg  |
| <b>Max. volume of single container</b>             | 10 L    |
| <b>Collection volume</b>                           | 11 L    |
| <b>Weight (product) approx.</b>                    | 322 kg  |

## Cabinet

|                                     |              |
|-------------------------------------|--------------|
| <b>Material of cabinet cladding</b> | Sheet steel  |
| <b>Cabinet colour</b>               | RAL 7035     |
| <b>Material of inner lining</b>     | Decor panels |
| <b>Colour of inner lining</b>       | RAL 7035     |
| <b>Base</b>                         | Classical    |
| <b>Base height approx.</b>          | 89 mm        |
| <b>Base colour</b>                  | RAL 7015     |

## Doors

|                               |                        |
|-------------------------------|------------------------|
| <b>No. of doors</b>           | 1                      |
| <b>Kind of door</b>           | Folding door           |
| <b>Material of door cover</b> | Sheet steel            |
| <b>Door colour</b>            | RAL 1018               |
| <b>Door hinge</b>             | Right                  |
| <b>Door operation</b>         | Classical              |
| <b>Door technology</b>        | Classical              |
| <b>Door handle</b>            | Bow handle matt nickel |
| <b>Lock</b>                   | Cylinder lock          |
| <b>Locking system</b>         | Open                   |
| <b>Locking points</b>         | 1-point                |

## Interior fittings

|                                      |             |
|--------------------------------------|-------------|
| <b>Material of interior fittings</b> | Sheet steel |
| <b>Colour of interior fittings</b>   | RAL 7035    |
| <b>Bottom tray</b>                   | Fixed       |
| <b>Pull-out shelf</b>                | Yes         |
| <b>Storage levels</b>                | 4           |
| <b>Storage areas</b>                 | 4           |
| <b>setting height approx.</b>        | 356 mm      |