



## CLASSIC line

Article Number: 29-201267-006

**Product Range**

Safety storage cabinet

**Product Category**

for clean rooms

## General

<b>Line</b>	CLASSIC
<b>Version</b>	pure
<b>Size</b>	XL
<b>Type</b>	90
<b>Storage type</b>	passive storage
<b>Functionality</b>	Storage
<b>Earthing connection</b>	Yes
<b>Connection socket</b>	Yes

## Test criteria and documentation

<b>TÜV Süd certificate no.</b>	Z1A 012906 0520
<b>TÜV-Süd certificate type</b>	GS
<b>TÜV-Süd High Quality Zertifikat</b>	Z2 012906 0513
<b>DIN EN 14470-1</b>	Yes
<b>DIN EN 16121/16122</b>	Yes
<b>CE conformity</b>	Yes

## Technical specifications

<b>Outer width approx.</b>	1194 mm
<b>Outer depth approx.</b>	612 mm
<b>Outer height approx.</b>	2045 mm
<b>Max. load bearing capacity per storage area</b>	75 kg
<b>Max. load</b>	360 kg
<b>Max. total weight</b>	815 kg
<b>Max. volume of single container</b>	30 L
<b>Collection volume</b>	33 L
<b>Weight (product) approx.</b>	530 kg

## Cabinet

<b>Material of cabinet cladding</b>	Sheet steel
<b>Cabinet colour</b>	RAL 9006
<b>Material of inner lining</b>	Stainless steel V2A
<b>Base</b>	Classical
<b>Base height approx.</b>	89 mm
<b>Base colour</b>	RAL 7015

## Doors

<b>No. of doors</b>	2
<b>Kind of door</b>	Wing door
<b>Material of door cover</b>	Sheet steel
<b>Door colour</b>	RAL 9006
<b>Door operation</b>	Classical
<b>Door technology</b>	Classical
<b>Door handle</b>	Bow handle matt nickel
<b>Lock</b>	Cylinder lock
<b>Locking system</b>	Open
<b>Locking points</b>	1-point

## Interior fittings

<b>Material of interior fittings</b>	Stainless steel V2A
<b>Bottom tray</b>	Fixed
<b>Storage shelf</b>	Yes
<b>Storage levels</b>	4
<b>Storage areas</b>	4
<b>setting height approx.</b>	394 mm