



TAP line

Article Number: 49-200975-028

Product Range

Safety storage cabinet

Product Category

Type 90 - flammable liquids

General

| | |
|----------------------------|------------------|
| Line | TAP |
| Version | standard connect |
| Design | C |
| Size | LL |
| Type | 90 |
| Storage type | active storage |
| Functionality | Filling |
| Earthing connection | Yes |
| Connection socket | Yes |

Test criteria and documentation

| | |
|--|-----------------|
| TÜV Süd certificate no. | Z1A 012906 0520 |
| TÜV-Süd certificate type | GS |
| TÜV-Süd High Quality Zertifikat | Z2 012906 0513 |
| DIN EN 14470-1 | Yes |
| DIN EN 16121/16122 | Yes |
| CE conformity | Yes |

Technical specifications

| | |
|--|---------|
| Outer width approx. | 894 mm |
| Outer depth approx. | 747 mm |
| Outer height approx. | 2045 mm |
| Max. load bearing capacity per storage area | 75 kg |
| Max. load | 225 kg |
| Max. total weight | 740 kg |
| Max. volume of single container | 30 L |
| Collection volume | 33 L |
| Weight (product) approx. | 500 kg |
| Potential-free contact | Yes |

Cabinet

| | |
|-------------------------------------|------------------------------|
| Material of cabinet cladding | Sheet steel |
| Cabinet colour | electrically conductive gray |
| Material of inner lining | Sheet steel |
| Colour of inner lining | electrically conductive gray |
| Base | Classical |
| Base height approx. | 89 mm |
| Base colour | RAL 7015 |

Doors

| | |
|-------------------------------|------------------------------|
| No. of doors | 2 |
| Kind of door | Wing door |
| Material of door cover | Sheet steel |
| Door colour | electrically conductive blue |
| Door operation | One-hand |
| Door technology | Classical |
| Door handle | Bow handle matt nickel |
| Lock | Cylinder lock |
| Locking system | Open |
| Locking points | 1-point |

Interior fittings

| | |
|--------------------------------------|------------------------------|
| Material of interior fittings | Sheet steel |
| Colour of interior fittings | electrically conductive gray |
| Bottom tray | Fixed |
| Storage shelf | Yes |
| Storage levels | 3 |
| Storage areas | 3 |
| setting height approx. | 341 mm |
| Accessories | Yes |
| Load adapter | Yes |
| Exhaust air monitoring | yes w/display |