

Article Number: 5.082.07

Product Range Safety equipment
Product Category



with imerstion tube act as flame arrester
Filling opening dia: 280 mm
Length of flame arrester: 150 mm
funnel exterior red powder coated
interior tin plated
immersion tube and flame arrester made
from brass, 2 '' thread
Self-closing lid in case of fire
via fusible
Testings:
FM-approved

Retail category	Funnels
Outer width	381 mm
Outer depth	355 mm
Outer height	406 mm
Weight (product)	4,5 kg