



Article Number: 5.09.010

Product Range

Safety equipment

Product Category

black, electrostatically conductive
Dimensions: 300 x 200 x 258 (L x W x H mm)
Filler dia: 56 mm
Tight closure, type approved receptacle
meets ADR / RID / IMDG coding / ICAO-TI.
Canister marking according to GefStoffV and BGV A8
Testings:
Quality control according to RAL-RG 726/1,
BAM-permission
Note:
In order to guarantee the tight closure of the
receptacle, screw down with a turning moment
of 20 Nm.
For this we recommend the usage of special pliers
item code 5.09.003.

Retail category	Safety containers
Retail product filter	for liquid hazardous substances
Outer width	195 mm
Outer depth	300 mm
Outer height	258 mm
Weight (product)	1,5 kg