



## COMPLEX line

Article Number: 59-200975-017

**Product Range**

Safety storage cabinet

**Product Category**

Type 90 - flammable liquids

## General

<b>Line</b>	COMPLEX
<b>Version</b>	standard connect
<b>Size</b>	LL
<b>Type</b>	90
<b>Storage type</b>	active storage
<b>Functionality</b>	Filling
<b>Earthing connection</b>	Yes
<b>Connection socket</b>	Yes

## Test criteria and documentation

<b>DIN EN 14470-1</b>	Yes
<b>DIN EN 16121/16122</b>	Yes
<b>CE conformity</b>	Yes

## Technical specifications

<b>Outer width approx.</b>	894 mm
<b>Outer depth approx.</b>	747 mm
<b>Outer height approx.</b>	2045 mm
<b>Max. load bearing capacity per storage area</b>	250 kg
<b>Max. load</b>	360 kg
<b>Max. total weight</b>	860 kg
<b>Max. volume of single container</b>	60 L
<b>Collection volume</b>	66 L
<b>Compressed air supply</b>	Yes
<b>Weight (product) approx.</b>	442 kg
<b>Potential-free contact</b>	Yes

## Cabinet

<b>Material of cabinet cladding</b>	Sheet steel
<b>Cabinet colour</b>	electrically conductive gray
<b>Material of inner lining</b>	Sheet steel
<b>Colour of inner lining</b>	electrically conductive gray
<b>Base</b>	Classical
<b>Base height approx.</b>	89 mm
<b>Base colour</b>	RAL 7015

## Doors

No. of doors	2
Kind of door	Wing door
Material of door cover	Sheet steel
Door colour	electrically conductive blue
Door operation	One-hand
Door technology	Classical
Door handle	Bow handle matt nickel
Lock	Cylinder lock
Locking system	Open
Locking points	1-point

## Interior fittings

Material of interior fittings	Sheet steel
Colour of interior fittings	electrically conductive gray
Bottom tray	Fixed
Bottom tray insert	Grating
Storage levels	1
Storage areas	1
setting height approx.	668 mm
Setting height filling container	190 - 380 mm

## Accessories

Number of filling points	1
Load adapter	Yes
Exhaust air monitoring	yes w/display
Ventilation system (w/ventilator)	yes w/enclosure and display
Display	Display
Alarm	yes - visual and acoustic