



COMPLEX line

Article Number: 59-201777-017

Product Range

Safety storage cabinet

Product Category

Type 90 - flammable liquids

General

| | |
|----------------------------|------------------|
| Line | COMPLEX |
| Version | standard connect |
| Size | XXL |
| Type | 90 |
| Storage type | active storage |
| Functionality | Filling |
| Earthing connection | Yes |
| Connection socket | Yes |

Test criteria and documentation

| | |
|---------------------------|-----|
| DIN EN 14470-1 | Yes |
| DIN EN 16121/16122 | Yes |
| CE conformity | Yes |

Technical specifications

| | |
|--|---------|
| Outer width approx. | 1645 mm |
| Outer depth approx. | 747 mm |
| Outer height approx. | 2045 mm |
| Max. load bearing capacity per storage area | 250 kg |
| Max. load | 720 kg |
| Max. total weight | 1080 kg |
| Max. volume of single container | 200 L |
| Collection volume | 220 L |
| Compressed air supply | Yes |
| Weight (product) approx. | 900 kg |
| Potential-free contact | Yes |

Cabinet

| | |
|-------------------------------------|------------------------------|
| Material of cabinet cladding | Sheet steel |
| Cabinet colour | electrically conductive gray |
| Material of inner lining | Sheet steel |
| Colour of inner lining | electrically conductive gray |
| Base | Classical |
| Base height approx. | 89 mm |
| Base colour | RAL 7015 |

Doors

| | |
|-------------------------------|------------------------------|
| No. of doors | 2 |
| Kind of door | Wing door |
| Material of door cover | Sheet steel |
| Door colour | electrically conductive blue |
| Door operation | Classical |
| Door technology | Classical |
| Door handle | Bow handle matt nickel |
| Lock | Cylinder lock |
| Locking system | Open |
| Locking points | 1-point |

Interior fittings

| | |
|---|------------------------------|
| Material of interior fittings | Sheet steel |
| Colour of interior fittings | electrically conductive gray |
| Bottom tray | Fixed |
| Bottom tray insert | Grating |
| Storage levels | 1 |
| Storage areas | 2 |
| setting height approx. | 1177 mm |
| Setting height filling container | 190 - 380 mm |

Accessories

| | |
|--|-----------------------------|
| Number of filling points | 1 |
| Load adapter | Yes |
| Exhaust air monitoring | yes w/display |
| Ventilation system (w/ventilator) | yes w/enclosure and display |
| Display | Display, multi-line |
| Alarm | yes - visual and acoustic |
| Zusatzausstattung | |