



Article Number: 59-30000-098

**Product Range**

Safety equipment

**Product Category**

black, electrostatically conductive  
Dimensions: 365 x 265 x 425 (L x W x H) in mm  
with shrink-wrapped sensor support,  
e.g. for capacitive level probe (I/O)

<b>HW-category</b>	Safety containers
<b>HW product filter</b>	Accessories DISPOSAL line
<b>Outer width approx.</b>	265 mm
<b>Outer depth approx.</b>	365 mm
<b>Outer height approx.</b>	425 mm
<b>Weight (product) approx.</b>	1,9 kg