



## BATTERY line

Article Number: 600121

**Product Range**

Safety storage cabinet

**Product Category**

Type 90 - lithium-ion  
batteries

## General

<b>Line</b>	BATTERY
<b>Version</b>	station connect
<b>Size</b>	XL
<b>Type</b>	90
<b>Storage type</b>	passive storage
<b>Functionality</b>	Charging
<b>Earthing connection</b>	Yes
<b>Connection socket</b>	Yes

## Test criteria and documentation

<b>DIN EN 14470-1</b>	Yes
<b>DIN EN 16121/16122</b>	Yes
<b>DIN EN IEC 61439-2</b>	Yes
<b>CE conformity</b>	Yes

## Technical specifications

<b>Outer width approx.</b>	1194 mm
<b>Outer depth approx.</b>	612 mm
<b>Outer height approx.</b>	2091 mm
<b>Max. load bearing capacity per storage area</b>	75 kg
<b>Max. load</b>	360 kg
<b>Max. total weight</b>	890 kg
<b>Max. volume of single container</b>	30 L
<b>Collection volume</b>	33 L
<b>Electrical sockets</b>	32
<b>Country code</b>	Type F: CEE 7/3
<b>Max. capacity of li-ion cell</b>	54 Ah
<b>Power supply</b>	400V - 50Hz - IEC 61439
<b>Weight (product) approx.</b>	550 kg
<b>Connector Type</b>	CEE 3P+N+E, 6h, red
<b>Potential-free contact</b>	Yes

## Cabinet

<b>Material of cabinet cladding</b>	Sheet steel
<b>Cabinet colour</b>	RAL 7035
<b>Material of inner lining</b>	Decor panels
<b>Colour of inner lining</b>	RAL 7035
<b>Base</b>	Set-back
<b>Base height approx.</b>	95 mm
<b>Base colour</b>	RAL 7015

## Doors

<b>No. of doors</b>	2
<b>Kind of door</b>	Wing door
<b>Material of door cover</b>	Sheet steel
<b>Door colour</b>	PANTONE 389 C
<b>Door operation</b>	Classical
<b>Door technology</b>	Classical
<b>Door handle</b>	Bow handle matt nickel
<b>Lock</b>	Cylinder lock
<b>Locking system</b>	Permanent
<b>Locking points</b>	2-point
<b>Backdraft lock</b>	yes

## Interior fittings

<b>Material of interior fittings</b>	Sheet steel
<b>Colour of interior fittings</b>	RAL 7035
<b>Centre partition wall</b>	Yes
<b>Bottom tray</b>	Fixed
<b>Bottom tray insert</b>	Perforated sheet insert
<b>Storage shelf</b>	Yes
<b>Storage levels</b>	4
<b>Storage areas</b>	8
<b>setting height approx.</b>	378 mm
<b>Accessories</b>	Yes
<b>Number of penetrations</b>	2
<b>Load adapter</b>	Yes
<b>Sensor Hub</b>	1
<b>Number of temperature monitors</b>	1
<b>Number of door status monitors</b>	2
<b>Signal warning light</b>	Yes
<b>Smoke detector</b>	Yes
<b>Temperature monitoring</b>	Yes
<b>Door status monitoring</b>	Yes
<b>Alarm</b>	yes - visual and acoustic