



BATTERY line

Article Number: 600137

Product Range

Safety storage cabinet

Product Category

Type 90 - lithium-ion
batteries

General

| | |
|----------------------------|-----------------|
| Line | BATTERY |
| Version | station connect |
| Size | XL |
| Type | 90 |
| Storage type | passive storage |
| Functionality | Charging |
| Earthing connection | Yes |
| Connection socket | Yes |

Test criteria and documentation

| | |
|---------------------------|-----|
| DIN EN 14470-1 | Yes |
| DIN EN 16121/16122 | Yes |
| DIN EN IEC 61439-2 | Yes |
| CE conformity | Yes |

Technical specifications

| | |
|--|-------------------------|
| Outer width approx. | 1194 mm |
| Outer depth approx. | 612 mm |
| Outer height approx. | 2091 mm |
| Max. load bearing capacity per storage area | 75 kg |
| Max. load | 360 kg |
| Max. total weight | 890 kg |
| Max. volume of single container | 30 L |
| Collection volume | 33 L |
| Electrical sockets | 32 |
| Country code | Type F: CEE 7/3 |
| Max. capacity of li-ion cell | 54 Ah |
| Power supply | 230V - 50Hz - IEC 61439 |
| Weight (product) approx. | 550 kg |
| Connector Type | CEE P+N+E, 6h, blue |
| Potential-free contact | Yes |

Cabinet

| | |
|-------------------------------------|--------------|
| Material of cabinet cladding | Sheet steel |
| Cabinet colour | RAL 7035 |
| Material of inner lining | Decor panels |
| Colour of inner lining | RAL 7035 |
| Base | Set-back |
| Base height approx. | 95 mm |
| Base colour | RAL 7015 |

Doors

| | |
|------------------------|------------------------|
| No. of doors | 2 |
| Kind of door | Wing door |
| Material of door cover | Sheet steel |
| Door colour | PANTONE 389 C |
| Door operation | Classical |
| Door technology | Classical |
| Door handle | Bow handle matt nickel |
| Lock | Cylinder lock |
| Locking system | Permanent |
| Locking points | 2-point |
| Backdraft lock | yes |

Interior fittings

| | |
|--------------------------------|-------------------------|
| Material of interior fittings | Sheet steel |
| Colour of interior fittings | RAL 7035 |
| Centre partition wall | Yes |
| Bottom tray | Fixed |
| Bottom tray insert | Perforated sheet insert |
| Storage shelf | Yes |
| Storage levels | 4 |
| Storage areas | 8 |
| setting height approx. | 378 mm |
| Accessories | Yes |
| Number of penetrations | 2 |
| Load adapter | Yes |
| Sensor Hub | 1 |
| Number of temperature monitors | 1 |
| Temperature monitoring | Yes |