



DEPOT line

Article Number: 70-201040-003

Product Range

Safety storage cabinet

Product Category

Gas cylinder - outside storage

General

Line	DEPOT
Size	L
Functionality	Storage
Earthing connection	Yes

Test criteria and documentation

Technical specifications

Outer width approx.	954 mm
Outer depth approx.	400 mm
Outer height approx.	2053 mm
Max. load bearing capacity per storage area	150 kg
Number of gas cylinder retaining belts	3
Weight (product) approx.	103 kg

Cabinet

Material of cabinet cladding	Sheet steel
Cabinet colour	RAL 9002
Material of inner lining	Sheet steel
Colour of inner lining	RAL 9002

Doors

No. of doors	2
Kind of door	Wing door
Material of door cover	Sheet steel
Door colour	RAL 9002
Door operation	Classical
Door technology	Classical
Door handle	Lever handle black PA
Lock	Cylinder lock
Locking system	Open
Locking points	3-point

Interior fittings

Material of interior fittings	Sheet steel
Colour of interior fittings	RAL 9002
Storage levels	1
Storage areas	1
setting height approx.	1970 mm

Zusatzausstattung

Number of inspection windows	2
------------------------------	---