



## ECO line

Article Number: 73-201460-021

**Product Range**

Safety storage cabinet

**Product Category**

Type G30 - gas storage

## General

<b>Line</b>	ECO
<b>Version</b>	standard
<b>Size</b>	XXL
<b>Type</b>	G30
<b>Functionality</b>	Storage
<b>Earthing connection</b>	Yes
<b>Connection socket</b>	Yes

## Test criteria and documentation

<b>TÜV Süd certificate no.</b>	Z1A 012906 0524
<b>TÜV-Süd certificate type</b>	GS
<b>TÜV-Süd High Quality Zertifikat</b>	Z2 012906 0513
<b>DIN EN 14470-2</b>	Yes
<b>DIN EN 16121/16122</b>	Yes
<b>CE conformity</b>	Yes

## Technical specifications

<b>Outer width approx.</b>	1395 mm
<b>Outer depth approx.</b>	596 mm
<b>Outer height approx.</b>	2030 mm
<b>Max. load bearing capacity per storage area</b>	400 kg
<b>Max. load</b>	400 kg
<b>Max. total weight</b>	975 kg
<b>Number of gas cylinder retaining belts</b>	4
<b>Weight (product) approx.</b>	575 kg

## Cabinet

<b>Material of cabinet cladding</b>	Sheet steel
<b>Cabinet colour</b>	RAL 7035
<b>Material of inner lining</b>	Decor panels
<b>Colour of inner lining</b>	RAL 7035

## Doors

<b>No. of doors</b>	2
<b>Kind of door</b>	Wing door
<b>Material of door cover</b>	Sheet steel
<b>Door colour</b>	RAL 3003
<b>Door operation</b>	Classical
<b>Door technology</b>	Classical
<b>Door handle</b>	Window handle matt chrome
<b>Lock</b>	Cylinder lock

## Interior fittings

<b>Material of interior fittings</b>	Sheet steel
<b>Colour of interior fittings</b>	RAL 7035
<b>setting height approx.</b>	1884 mm
<b>Fitting holder</b>	Yes - Position A
<b>Number of cylinder holders</b>	1