



## COOL line

Article Number: 89-200977-041

**Product Range**

Safety storage cabinet

**Product Category**

Type 90 - cooled storage

## General

<b>Line</b>	COOL
<b>Version</b>	dual connect
<b>Size</b>	XL
<b>Type</b>	90
<b>Storage type</b>	passive storage
<b>Functionality</b>	Storage
<b>Earthing connection</b>	Yes
<b>Connection socket</b>	Yes

## Test criteria and documentation

<b>TÜV Süd certificate no.</b>	Z1A 012906 0520
<b>TÜV-Süd certificate type</b>	GS
<b>TÜV-Süd High Quality Zertifikat</b>	Z2 012906 0513
<b>DIN EN 14470-1</b>	Yes
<b>DIN EN 16121/16122</b>	Yes

## Technical specifications

<b>Outer width approx.</b>	894 mm
<b>Outer depth approx.</b>	747 mm
<b>Outer height approx.</b>	2045 mm
<b>Max. load bearing capacity per storage area</b>	40 kg
<b>Max. load</b>	240 kg
<b>Max. total weight</b>	715 kg
<b>Max. volume of single container</b>	5 L
<b>Collection volume</b>	5,5 L
<b>Power supply</b>	230V - 50Hz - IEC 61439
<b>Weight (product) approx.</b>	499 kg
<b>Temperaturprofil</b>	+3°C - +16°C
<b>Connector Type</b>	Type E+F: CEE 7/7
<b>Potential-free contact</b>	Yes

## Cabinet

<b>Material of cabinet cladding</b>	Sheet steel
<b>Cabinet colour</b>	RAL 7035
<b>Material of inner lining</b>	Decor panels
<b>Colour of inner lining</b>	RAL 7035
<b>Base</b>	Classical
<b>Base height approx.</b>	89 mm
<b>Base colour</b>	RAL 7015

## Doors

No. of doors	1
Kind of door	Wing door
Material of door cover	Sheet steel
Door colour	RAL 9016
Door hinge	Right
Door operation	Classical
Door technology	Classical
Door handle	Bow handle matt nickel
Lock	Cylinder lock
Locking system	Open
Locking points	1-point

## Interior fittings

Material of interior fittings	Sheet steel
Colour of interior fittings	RAL 9016
Bottom tray	Fixed
Bottom tray insert	Perforated sheet insert
Storage shelf	Yes
Storage levels	8
Storage areas	8
setting height approx.	628 mm

## Accessories

Number of penetrations	1
Load adapter	Yes
Exhaust air monitoring	Yes
Zusatzausstattung	