

Ausschreibungstext

Article Number: 1.41.203

Product Range Safety equipment

Product Category

- square -

dim.: 1200 x 1200 x 285 (W x D x H mm)

Collection volume: 210 l

Sheet steel painted to RAL 5012 lightblue,
material strength 3 mm

with galvanised removable grating.

Ground clearance approx. 100 mm.

load 1000 kg

suitable for flammable liquids F+ F
and water polluting liquids WGK 1-3

Testings:

with declaration of conformity (ÜHP)

according to StawaR

Tested by TÜV

- square -

dim.: 1200 x 1200 x 285 (W x D x H mm)

Collection volume: 210 l

Sheet steel painted to RAL 5012 lightblue,
material strength 3 mm

with galvanised removable grating.

Ground clearance approx. 100 mm.

load 1000 kg

suitable for flammable liquids F+ F
and water polluting liquids WGK 1-3

Testings:

with declaration of conformity (ÜHP)

according to StawaR

Tested by TÜV

HW-category

Collecting trays

Outer width approx.

1200 mm

Outer depth approx.

1200 mm

Outer height approx.

285 mm