

Ausschreibungstext

Article Number: 1.41.301

Product Range Safety equipment

Product Category

Approx. dim.: 800 x 800 x 465 (WxDxH in mm)

Collection volume: 210 l

Material strength 3 mm,

with galvanised removable grating,

skids with 100 mm underclearance,

Load: 250 kg

Suitable for flammable liquids F+, F und

for water polluting liquids WGK 1-3

Testings:

Declaration of conformity (ÜHP)

according to StawaR,

TÜV-tested

Approx. dim.: 800 x 800 x 465 (WxDxH in mm)

Collection volume: 210 l

Material strength 3 mm,

with galvanised removable grating,

skids with 100 mm underclearance,

Load: 250 kg

Suitable for flammable liquids F+, F und

for water polluting liquids WGK 1-3

Testings:

Declaration of conformity (ÜHP)

according to StawaR,

TÜV-tested

HW-category

Collecting trays

Outer width approx.

800 mm

Outer depth approx.

800 mm

Outer height approx.

465 mm