

Article Number: 1.52.221

**Product Range** Safety equipment

**Product Category**

INSULATED, GALVANISED VERSION:

Outer dim.: 1950 x 2350 x 2340(WxDxH in mm)

Inner dim.: 1772 x 2062 x 2051 (WxDxH in mm)

Capacity: 6300 l

Approval for storage of water polluting liquids

WGK 1 - 3, flammable liquids, F+, F outdoors or in building in accordance with the specific fire protection regulations.

Construction of container:

- Wall and ceiling elements made from galvanised trapezoidal sections, floor sections made from sheet steel.

- 1 leaf, galvanised door, 1294 mm wide and 1996 mm high, the door is hung on the right, mounted on the longitudinal side.

- Single-point locking

- Mortise lock with door handles and security lock with 2 keys.

- The accessible roof is designed for 125 kg/m<sup>2</sup> snow load.

- Drainage through inner-lying gutters.

- Bottom tray made from 3 mm thick, galvanised sheet steel, welded liquid-tight, covered with PE-foil.

- Standing level made from galvanised, removable gratings, load 1000 kg/m<sup>2</sup>.

- Walls, roof and door thermally insulated with insulation panels (45 mm).

Testing:

General national technical approval Z-38.5-94 of the Deutsche Institut für Bautechnik (DIBt) Berlin

INSULATED, GALVANISED VERSION:

Outer dim.: 1950 x 2350 x 2340(WxDxH in mm)

Inner dim.: 1772 x 2062 x 2051 (WxDxH in mm)

# Ausschreibungstext

Capacity: 6300 l

Approval for storage of water polluting liquids  
WGK 1 - 3, flammable liquids, F+, F outdoors or in  
building in accordance with the specific fire  
protection regulations.

Construction of container:

- Wall and ceiling elements made from galvanised trapezoidal sections, floor sections made from sheet steel.
- 1 leaf, galvanised door, 1294 mm wide and 1996 mm high, the door is hung on the right, mounted on the longitudinal side.
- Single-point locking
- Mortise lock with door handles and security lock with 2 keys.
- The accessible roof is designed for 125 kg/m<sup>2</sup> snow load.
- Drainage through inner-lying gutters.
- Bottom tray made from 3 mm thick, galvanised sheet steel, welded liquid-tight, covered with PE-foil.
- Standing level made from galvanised, removable gratings, load 1000 kg/m<sup>2</sup>.
- Walls, roof and door thermally insulated with insulation panels (45 mm).

Testing:

General national technical approval Z-38.5-94 of the Deutsche Institut für Bautechnik (DIBt) Berlin

<b>HW-category</b>	Safety storage container
<b>Outer width approx.</b>	2350 mm
<b>Outer depth approx.</b>	1950 mm
<b>Outer height approx.</b>	2340 mm