

# Ausschreibungstext

---

Article Number: 1.52.411

**Product Range** Safety equipment

**Product Category**

GALVANISED VERSION:

Dimension: 915 x 2350 x 2340 (LxWxH in mm)

Capacity: 3000 l

Approval for storage of water polluting liquids  
WGK 1 - 3, flammable liquids, F+, F outdoors or in  
building in accordance with the specific fire  
protection regulations.

Construction of container:

- Wall and ceiling elements made from galvanised trapezoidal sections, floor sections made from sheet steel.
- 1 leaf, galvanised door, 1294 mm wide and 1996 mm high, the door is hung on the right, mounted on the longitudinal side.
- Single-point locking
- Mortise lock with door handles and security lock with 2 keys.
- The accessible roof is designed for 125 kg/m<sup>2</sup> snow load.
- Drainage through inner-lying gutters.
- Bottom tray made from 3 mm thick, galvanised sheet steel, welded liquid-tight.
- Standing level made from galvanised, removable gratings, load 1000 kg/m<sup>2</sup>.

Testing:

General national technical approval Z-38.5-94 of the Deutsche Institut für Bautechnik (DIBt) Berlin

GALVANISED VERSION:

Dimension: 915 x 2350 x 2340 (LxWxH in mm)

Capacity: 3000 l

Approval for storage of water polluting liquids  
WGK 1 - 3, flammable liquids, F+, F outdoors or in  
building in accordance with the specific fire  
protection regulations.

# Ausschreibungstext

Construction of container:

- Wall and ceiling elements made from galvanised trapezoidal sections, floor sections made from sheet steel.
- 1 leaf, galvanised door, 1294 mm wide and 1996 mm high, the door is hung on the right, mounted on the longitudinal side.
- Single-point locking
- Mortise lock with door handles and security lock with 2 keys.
- The accessible roof is designed for 125 kg/m<sup>2</sup> snow load.
- Drainage through inner-lying gutters.
- Bottom tray made from 3 mm thick, galvanised sheet steel, welded liquid-tight.
- Standing level made from galvanised, removable gratings, load 1000 kg/m<sup>2</sup>.

Testing:

General national technical approval Z-38.5-94 of the Deutsche Institut für Bautechnik (DIBt) Berlin

|                             |                          |
|-----------------------------|--------------------------|
| <b>HW-category</b>          | Safety storage container |
| <b>Outer width approx.</b>  | 2350 mm                  |
| <b>Outer depth approx.</b>  | 915 mm                   |
| <b>Outer height approx.</b> | 2340 mm                  |