

Article Number: 1.52.413

Product Range Safety equipment

Product Category

GALVANISED VERSION:

Outer dim.: 2350 x 4020 x 2340 (LxWxH in mm)

Inner dim.: 2152 x 3935 x 2051 (LxWxH in mm)

Capacity: 10000 l

Approval for storage of water polluting liquids

WGK 1 - 3, flammable liquids, F+, F outdoors or in building in accordance with the specific fire protection regulations.

Construction of container:

- Wall and ceiling elements made from galvanised trapezoidal sections, floor sections made from sheet steel.
- 1 leaf, galvanised door, 1294 mm wide and 1996 mm high, the door is hung on the right, mounted on the longitudinal side (optionally on the longitudinal or narrow side).
- Single-point locking
- Mortise lock with door handles and security lock with 2 keys.
- The accessible roof is designed for 125 kg/m² snow load.
- Drainage through inner-lying gutters.
- Bottom tray made from 3 mm thick, galvanised sheet steel, welded liquid-tight.
- Standing level made from galvanised, removable gratings, load 1000 kg/m².

Testing:

General national technical approval Z-38.5-94 of the Deutsche Institut für Bautechnik (DIBt) Berlin

GALVANISED VERSION:

Outer dim.: 2350 x 4020 x 2340 (LxWxH in mm)

Inner dim.: 2152 x 3935 x 2051 (LxWxH in mm)

Capacity: 10000 l

Approval for storage of water polluting liquids

Ausschreibungstext

27.03.2026 11:09

WGK 1 - 3, flammable liquids, F+, F outdoors or in building in accordance with the specific fire protection regulations.

Construction of container:

- Wall and ceiling elements made from galvanised trapezoidal sections, floor sections made from sheet steel.
- 1 leaf, galvanised door, 1294 mm wide and 1996 mm high, the door is hung on the right, mounted on the longitudinal side (optionally on the longitudinal or narrow side).
- Single-point locking
- Mortise lock with door handles and security lock with 2 keys.
- The accessible roof is designed for 125 kg/m² snow load.
- Drainage through inner-lying gutters.
- Bottom tray made from 3 mm thick, galvanised sheet steel, welded liquid-tight.
- Standing level made from galvanised, removable gratings, load 1000 kg/m².

Testing:

General national technical approval Z-38.5-94 of the Deutsche Institut für Bautechnik (DIBt) Berlin

HW-category	Safety storage container
Outer width approx.	4020 mm
Outer depth approx.	2350 mm
Outer height approx.	2340 mm