

Article Number: 1.61.004

Product Range Safety equipment

Product Category

Dim.: appr. 2470 x 870 x 270 (W x D x H in mm),
collection volume: 225 l

load bearing capacity: 1800 kg

low tare weight: 89 kg

plastic structure made from extruded
laminate (PE-HD),

with stable PE perforated plate as standing level
accessiuble due to 100 mm base design.

suitable for water polluting,

non-flammable liquids WGK 1-3,

Tested:

General national technical approval of
DIBT-Berlin, MPA-tested, TÜV-tested

Dim.: appr. 2470 x 870 x 270 (W x D x H in mm),
collection volume: 225 l

load bearing capacity: 1800 kg

low tare weight: 89 kg

plastic structure made from extruded
laminate (PE-HD),

with stable PE perforated plate as standing level
accessiuble due to 100 mm base design.

suitable for water polluting,

non-flammable liquids WGK 1-3,

Tested:

General national technical approval of
DIBT-Berlin, MPA-tested, TÜV-tested

HW-category

Collecting trays

Outer width approx.

870 mm

Outer depth approx.

2470 mm

Outer height approx.

270 mm