

Article Number: 1.96.100

Product Range Safety equipment

Product Category

parts in contact with medium made from
stainless steel 1.4301 and PTFE

electro-statically conductive

immersion depth: 910 mm

delivery rate per stroke: 560 ml

immersion depth: 1030 mm

immersion tube dia: 32 mm

parts in contact with medium made from
stainless steel 1.4301 and PTFE

electro-statically conductive

immersion depth: 910 mm

delivery rate per stroke: 560 ml

immersion depth: 1030 mm

immersion tube dia: 32 mm

HW-category

Pumps