

Article Number: 1.96.105

Product Range Safety equipment

Product Category

drum thread and non-return valve
parts in contact with medium made from
stainless steel 1.4301 and PTFE
electro-statically conductive
unscrewable outlet hose
immersion depth: 910 mm
delivery rate per stroke: 560 ml
immersion depth: 1030 mm
immersion tube dia: 32 mm

drum thread and non-return valve
parts in contact with medium made from
stainless steel 1.4301 and PTFE
electro-statically conductive
unscrewable outlet hose
immersion depth: 910 mm
delivery rate per stroke: 560 ml
immersion depth: 1030 mm
immersion tube dia: 32 mm

HW-category

Pumps