

Article Number: 1.96.130

Product Range Safety equipment

Product Category

gaskets made from EPDM

pump is gas-tight and can be completely blocked with two ball valves.

immersion depth 600 mm

suitable for stainless steel drums usually used in laboratories

Flow rate: 10 l/min. with R 2 " -fine thread

gaskets made from EPDM

pump is gas-tight and can be completely blocked with two ball valves.

immersion depth 600 mm

suitable for stainless steel drums usually used in laboratories

Flow rate: 10 l/min. with R 2 " -fine thread

HW-category

Pumps