

Article Number: 11.90.920

Product Range Safety equipment

Product Category

Fine granulate made from thermoset polymers,
can be used for all liquids,
absorbs up to 75 times its own weight,
economical and problem-free measure,
does not trigger any dangerous reactions.

also usable in rain, (ph-neutral)

Indicates the binder's saturation by dry deposit
on the surface.

Barrier formation possible, swells,
has an indicator function - Indicator transition:
acids (yellow) / lyes (red)

Testings:

Tested and approved by MPA NRW, Dortmund
and also testec by the Hygiene Institutue
in Gelsenkirchen.

Fine granulate made from thermoset polymers,
can be used for all liquids,
absorbs up to 75 times its own weight,
economical and problem-free measure,
does not trigger any dangerous reactions.

also usable in rain, (ph-neutral)

Indicates the binder's saturation by dry deposit
on the surface.

Barrier formation possible, swells,
has an indicator function - Indicator transition:
acids (yellow) / lyes (red)

Testings:

Tested and approved by MPA NRW, Dortmund
and also testec by the Hygiene Institutue
in Gelsenkirchen.

HW-category	Emergency products
Outer width approx.	140 mm
Outer depth approx.	140 mm
Outer height approx.	265 mm