

Article Number: 11.90.930

**Product Range** Safety equipment

**Product Category**

Fine granulate made from thermoset polymers,  
can be used for all liquids,  
absorbs up to 75 times its own weight,  
economical and problem-free measure,  
does not trigger any dangerous reactions.

also usable in rain, (ph-neutral)

Indicates the binder's saturation by dry deposit  
on the surface.

Barrier formation possible, swells,  
has an indicator function - Indicator transition:  
acids (yellow) / lyes (red)

Testings:

Tested and approved by MPA NRW, Dortmund  
and also tested by the Hygiene Institute  
in Gelsenkirchen.

Fine granulate made from thermoset polymers,  
can be used for all liquids,  
absorbs up to 75 times its own weight,  
economical and problem-free measure,  
does not trigger any dangerous reactions.

also usable in rain, (ph-neutral)

Indicates the binder's saturation by dry deposit  
on the surface.

Barrier formation possible, swells,  
has an indicator function - Indicator transition:  
acids (yellow) / lyes (red)

Testings:

Tested and approved by MPA NRW, Dortmund  
and also tested by the Hygiene Institute  
in Gelsenkirchen.

|                             |                    |
|-----------------------------|--------------------|
| <b>HW-category</b>          | Emergency products |
| <b>Outer width approx.</b>  | 24 mm              |
| <b>Outer depth approx.</b>  | 39 mm              |
| <b>Outer height approx.</b> | 20 mm              |