

filter unit line

Article Number: 2.00.398

Product Range Safety equipment

Product Category

HW-category	Monitoring
Line	filter unit
CE conformity	Yes
Outer width approx.	460 mm
Outer depth approx.	415 mm
Outer height approx.	325 mm
Power supply	230V - 50Hz - IEC 61439
Connector Type	Type E+F: CEE 7/7
Potential-free contact	Yes
Exhaust air monitoring	Yes
Material of product	Sheet steel
Colour of product	Silver with pearlescent effect
Display	yes - LED
Activated Carbon Filter	yes - interchangeable
Filter Medium	according to substance list
Particle Filter	yes - interchangeable
Power of Activated Carbon Filter	30% of the filling quantity of the specified media
ATEX-Conformity	CE Ex II (3) G [n T4]
Low Voltage Directive 2006/95/EG	yes
PTB approval	yes - no. 14 ATEX D027
Noise Level	low noise

Monitorung of Filter	yes - changing intervall
Alarm	yes - visual and acoustic
IoT connectivity	radio - BT
Product Accessories	2.00.393