

## ACID line

Article Number: 20-081167-032

**Product Range** Safety storage cabinet

**Product Category** Non-flammable media

ACID line safety storage cabinets are optimised specifically for the storage of acids and lye. The varied additional functionalities of the cabinets of the ACID line increase workplace safety and comfort.

- **Health**  
Innovative design enables optimised air exchange.
- **Safety**  
All doors of the ACID line cabinets are separately lockable to provide access control and increase security.
- **Working safety**  
Highly media-resistant safety storage cabinets for the safe storage of aggressive substances.

|  |                 |
|--|-----------------|
| <b>Line</b>  | ACID            |
| <b>Storage type</b>                                | passive storage |
| <b>Functionality</b>                               | Storage         |
| <b>Connection socket</b>                           | Yes             |
| <b>TÜV-Süd certificate type</b>                    | GS              |
| <b>DIN EN 16121/16122</b>                          | Yes             |
| <b>Outer width approx.</b>                         | 1100 mm         |
| <b>Outer depth approx.</b>                         | 609 mm          |
| <b>Outer height approx.</b>                        | 805 mm          |
| <b>Max. load bearing capacity per storage area</b> | 40 kg           |
| <b>Material of cabinet cladding</b>                | Decor panels    |
| <b>Cabinet colour</b>                              | RAL 7035        |
| <b>Base</b>  | Classical       |
| <b>Base height approx.</b>                         | 35 mm           |
| <b>Base colour</b>                                 | RAL 7015        |

|                                      |                        |
|--------------------------------------|------------------------|
| <b>Kind of door</b>                  | Wing door              |
| <b>Door colour</b>                   | RAL 7035               |
| <b>Door handle</b>                   | Bow handle matt nickel |
| <b>Lock</b>                          | Cylinder lock          |
| <b>Locking system</b>                | Open                   |
| <b>Material of interior fittings</b> | PE                     |
| <b>Bottom tray</b>                   | Extendable             |
| <b>Pull-out shelf</b>                | Yes                    |
| <b>Storage levels</b>                | 2                      |
| <b>Storage areas</b>                 | 4                      |
| <b>setting height approx.</b>        | 350 mm                 |