

## CLASSIC line

Article Number: 29-200967-050

|                         |                             |
|-------------------------|-----------------------------|
| <b>Product Range</b>    | Safety storage cabinet      |
| <b>Product Category</b> | Type 90 - flammable liquids |

Your classical standard solution for the storage of hazardous substances: The CLASSIC line – highest level of fire protection and as practicable as you require.

- **Health**  
Ventilation on each cabinet level provides optimised air exchange.
- **Safety**  
In case of fire, a thermocouple automatically initiates the uninterrupted closing of the doors.
- **Working safety**  
Equipotential bonding saddles as a standard on the cabinet help to prevent spark formation.

|  |                 |
|--|-----------------|
| <b>Line</b>  | CLASSIC         |
| <b>Type</b>  | 90              |
| <b>Storage type</b>                                | passive storage |
| <b>Functionality</b>                               | Storage         |
| <b>Earthing connection</b>                         | Yes             |
| <b>Connection socket</b>                           | Yes             |
| <b>TÜV-Süd certificate type</b>                    | GS              |
| <b>DIN EN 14470-1</b>                              | Yes             |
| <b>DIN EN 16121/16122</b>                          | Yes             |
| <b>CE conformity</b>                               | Yes             |
| <b>Outer width approx.</b>                         | 894 mm          |
| <b>Outer depth approx.</b>                         | 612 mm          |
| <b>Outer height approx.</b>                        | 2045 mm         |
| <b>Max. load bearing capacity per storage area</b> | 60 kg           |

|                                      |                        |
|--------------------------------------|------------------------|
| <b>Material of cabinet cladding</b>  | Sheet steel            |
| <b>Cabinet colour</b>                | RAL 7035               |
| <b>Base</b>                          | Classical              |
| <b>Base height approx.</b>           | 89 mm                  |
| <b>Base colour</b>                   | RAL 7015               |
| <b>Kind of door</b>                  | Wing door              |
| <b>Door colour</b>                   | RAL 1018               |
| <b>Door handle</b>                   | Bow handle matt nickel |
| <b>Lock</b>                          | Cylinder lock          |
| <b>Locking system</b>                | Open                   |
| <b>Material of interior fittings</b> | Sheet steel            |
| <b>Bottom tray</b>                   | Fixed                  |
| <b>Pull-out shelf</b>                | Yes                    |
| <b>Storage levels</b>                | 3                      |
| <b>Storage areas</b>                 | 3                      |
| <b>setting height approx.</b>        | 502 mm                 |