

Article Number: 3.107.57

**Product Range** Safety equipment

**Product Category**

Sheet steel interior tin plated,  
exterior red powder coated,  
Self-closing opening,  
stainless steel flame arrester in can opening  
automatic pressure/vacuum compensation  
Dim.: 241 x337 ( dia x H in mm )  
galvanised metal hose, length: approx. 229 mm  
Diameter of hose: approx. 16 mm  
Marking prepared according to GefStoffV  
and BGV A8.  
Testings: FM, UL, TÜV-GS

Sheet steel interior tin plated,  
exterior red powder coated,  
Self-closing opening,  
stainless steel flame arrester in can opening  
automatic pressure/vacuum compensation  
Dim.: 241 x337 ( dia x H in mm )  
galvanised metal hose, length: approx. 229 mm  
Diameter of hose: approx. 16 mm  
Marking prepared according to GefStoffV  
and BGV A8.  
Testings: FM, UL, TÜV-GS

**HW-category**

Safety containers

**Outer height approx.**

349 mm