

Article Number: 3.119.67

Product Range Safety equipment

Product Category

Sheet steel interior tin plated,
exterior red powder coated,
Self-closing opening,
stainless steel flame arrester in can opening
automatic pressure/vacuum compensation
Dim.: 298 x 445 (dia x H in mm)
galvanised metal hose, length: approx. 229 mm
Diameter of hose: approx. 16 mm
Marking prepared according to GefStoffV
and BGV A8.
Testings: FM, UL, TÜV-GS

Sheet steel interior tin plated,
exterior red powder coated,
Self-closing opening,
stainless steel flame arrester in can opening
automatic pressure/vacuum compensation
Dim.: 298 x 445 (dia x H in mm)
galvanised metal hose, length: approx. 229 mm
Diameter of hose: approx. 16 mm
Marking prepared according to GefStoffV
and BGV A8.
Testings: FM, UL, TÜV-GS

HW-category

Safety containers

Outer height approx.

445 mm