

Article Number: 4.271.10

Product Range Safety equipment

Product Category

capacity: approx. 48 litres

outside dimensions: 610 x 496 x 845 (WxDxH) mm

basin (inside): 603 x 406 x 222 (WxDxH) mm

Basin, lid and frame made from galvanised sheet steel, red coated.

3/4"- drain plug in basin bottom for selective emptying.

Slow, independent closing of the lid via pneumatic cylinder.

Testing: FM-approved

capacity: approx. 48 litres

outside dimensions: 610 x 496 x 845 (WxDxH) mm

basin (inside): 603 x 406 x 222 (WxDxH) mm

Basin, lid and frame made from galvanised sheet steel, red coated.

3/4"- drain plug in basin bottom for selective emptying.

Slow, independent closing of the lid via pneumatic cylinder.

Testing: FM-approved

HW-category	Cleaning tanks
Outer width approx.	406 mm
Outer depth approx.	610 mm
Outer height approx.	222 mm