

Ausschreibungstext

Article Number: 4.271.40

Product Range Safety equipment

Product Category

capacity: approx. 2 x 15 litres

outside dimensions: 610 x 496 x 845 mm (W x D x H)

basin (inside): 2x 298 x 406 x 140 mm(W x D x H)

Basin, lid and frame made from
galvanised sheet steel, red coated.

For cleaning of extremely contaminated components.

1. chamber: pre-cleaning,

2. chamber: final cleaning

3/4"- drain plug in basin bottom for
selective emptying.

Testing: FM-approved

capacity: approx. 2 x 15 litres

outside dimensions: 610 x 496 x 845 mm (W x D x H)

basin (inside): 2x 298 x 406 x 140 mm(W x D x H)

Basin, lid and frame made from
galvanised sheet steel, red coated.

For cleaning of extremely contaminated components.

1. chamber: pre-cleaning,

2. chamber: final cleaning

3/4"- drain plug in basin bottom for
selective emptying.

Testing: FM-approved

HW-category

Cleaning tanks

Outer width approx.

406 mm

Outer depth approx.

610 mm

Outer height approx.

222 mm