

Article Number: 4.273.11

Product Range Safety equipment

Product Category

capacity: approx. 48 litres

outside dimensions: 610 x 496 x 273 mm (W x D x H)

basin (inside): 603 x 406 x 273 mm (W x D x H)

For positioning on a workbench.

Basin and lid made from

galvanised sheet steel, red coated.

self-closing lid in case of fire

3/4"- drain plug in basin bottom for

selective emptying.

Testing: FM-approved

capacity: approx. 48 litres

outside dimensions: 610 x 496 x 273 mm (W x D x H)

basin (inside): 603 x 406 x 273 mm (W x D x H)

For positioning on a workbench.

Basin and lid made from

galvanised sheet steel, red coated.

self-closing lid in case of fire

3/4"- drain plug in basin bottom for

selective emptying.

Testing: FM-approved

HW-category	Cleaning tanks
Outer width approx.	406 mm
Outer depth approx.	610 mm
Outer height approx.	222 mm