

Article Number: 4.273.22

Product Range Safety equipment

Product Category

capacity:approx. 97 litres

outside dimensions: 895 x 496 x 336 mm (W x D x H)

basin (inside): 889 x 406 x 336 mm (W x D x H)

For positioning on a workbench.

Basin, lid and frame made from galvanised sheet steel, red coated.

self-closing lid in case of fire

3/4"- drain plug in basin bottom for selective emptying

Testing: FM-approved

capacity:approx. 97 litres

outside dimensions: 895 x 496 x 336 mm (W x D x H)

basin (inside): 889 x 406 x 336 mm (W x D x H)

For positioning on a workbench.

Basin, lid and frame made from galvanised sheet steel, red coated.

self-closing lid in case of fire

3/4"- drain plug in basin bottom for selective emptying

Testing: FM-approved

HW-category	Cleaning tanks
Outer width approx.	406 mm
Outer depth approx.	895 mm
Outer height approx.	305 mm