

Article Number: 5.082.07

Product Range Safety equipment

Product Category

with immersion tube act as flame arrester

Filling opening dia: 280 mm

Length of flame arrester: 150 mm

funnel exterior red powder coated

interior tin plated

immersion tube and flame arrester made

from brass, 2 " thread

Self-closing lid in case of fire

via fusible

Testings:

FM-approved

with immersion tube act as flame arrester

Filling opening dia: 280 mm

Length of flame arrester: 150 mm

funnel exterior red powder coated

interior tin plated

immersion tube and flame arrester made

from brass, 2 " thread

Self-closing lid in case of fire

via fusible

Testings:

FM-approved

HW-category	Funnels
Outer width approx.	381 mm
Outer depth approx.	355 mm
Outer height approx.	406 mm