

## DISPOSAL line

Article Number: 500026

<b>Product Range</b>	Safety storage cabinet
<b>Product Category</b>	Type 90 - flammable liquids

Specially designed to store different chemical wastes, the DISPOSAL line is equipped with varied additional functions to make work easier and safer. From the great variety of optional extras, choose those which are ideally suited to your laboratory. Create your own individual work environment tailored to your requirements and work processes.

- **Technical ventilation**

Object and air curtain extraction during filling minimise the explosive atmosphere.

- **Safety**

Secure media disposal or transfer in containers up to 10 litres (2.64 gal) in accordance with TRGS 509 (active storage).

- **Working safety**

Conductive powder coating as a standard and integrated earthing system according to TRGS 727.

- **Monitoring with DÜPERTHAL connect**

Including hardware for monitoring fill level and prepared for online use of monitoring data in the DÜPERTHAL connect app.

<b>Line</b>	DISPOSAL
<b>Type</b>	90
<b>Storage type</b>	active storage
<b>Functionality</b>	Filling
<b>Earthing connection</b>	Yes
<b>Connection socket</b>	Yes
<b>TÜV-Süd certificate type</b>	GS
<b>DIN EN 14470-1</b>	Yes
<b>DIN EN 16121/16122</b>	Yes
<b>CE conformity</b>	Yes

<b>Outer width approx.</b>	1100 mm
<b>Outer depth approx.</b>	594 mm
<b>Outer height approx.</b>	631 mm
<b>Max. load bearing capacity per storage area</b>	45 kg
<b>Potential-free contact</b>	Yes
<b>Material of cabinet cladding</b>	Sheet steel
<b>Cabinet colour</b>	electrically conductive gray
<b>Base</b>	Classical
<b>Base height approx.</b>	35 mm
<b>Base colour</b>	RAL 7015
<b>Kind of door</b>	Wing door
<b>Door colour</b>	electrically conductive blue
<b>Door handle</b>	Bow handle matt nickel
<b>Lock</b>	Cylinder lock
<b>Locking system</b>	Open

<b>Material of interior fittings</b>	Sheet steel
<b>Centre partition wall</b>	Yes
<b>Bottom tray</b>	Extendable
<b>Bottom tray insert</b>	Container insert
<b>Storage levels</b>	1
<b>Storage areas</b>	2
<b>setting height approx.</b>	400 mm
<b>Accessories</b>	Yes
<b>Number of level monitors</b>	2
<b>Number of container</b>	4
<b>Number of penetrations</b>	2
<b>Container size</b>	10 L
<b>Level monitoring</b>	yes w/display
<b>Display</b>	yes - touch display