

Article Number: 59-10000-098

Product Range Safety equipment

Product Category

black, electrostatically conductive

Dimensions: 298 x 198 x 264 (L x W x H) in mm

with shrink-wrapped sensor support,

e.g. for capacitive level probe (I/O)

black, electrostatically conductive

Dimensions: 298 x 198 x 264 (L x W x H) in mm

with shrink-wrapped sensor support,

e.g. for capacitive level probe (I/O)

HW-category

Safety containers

Outer width approx.

298 mm

Outer depth approx.

198 mm

Outer height approx.

264 mm