

## COMPLEX line

Article Number: 59-201777-017

<b>Product Range</b>	Safety storage cabinet
<b>Product Category</b>	Type 90 - flammable liquids

The COMPLEX line Type 90 from DÜPERTHAL is a certified system solution specially designed for the removal of media from drums into smaller containers. The easy startup due to ready to plug-in, pre-assembled connections enables flexible work processes and more efficient organisation of the internal value chain.

- **Technical ventilation**

Object and air curtain extraction directly at the tap minimize the explosive atmosphere when filling.

- **Safety**

Safe media extraction from canisters and drums into smaller containers in accordance with TRGS 509 (active storage).

- **Working safety**

Conductive powder coating as a standard and integrated earthing system according to TRGS 727.

- **Monitoring with DÜPERTHAL connect**

Including hardware for monitoring fill level and prepared for online use of monitoring data in the DÜPERTHAL connect app.

<b>Line</b>	COMPLEX
<b>Type</b>	90
<b>Storage type</b>	active storage
<b>Functionality</b>	Filling
<b>Earthing connection</b>	Yes
<b>Connection socket</b>	Yes

<b>DIN EN 14470-1</b>	Yes
<b>DIN EN 16121/16122</b>	Yes
<b>CE conformity</b>	Yes
<b>Outer width approx.</b>	1645 mm
<b>Outer depth approx.</b>	747 mm
<b>Outer height approx.</b>	2045 mm
<b>Max. load bearing capacity per storage area</b>	250 kg
<b>Compressed air supply</b>	Yes
<b>Potential-free contact</b>	Yes
<b>Material of cabinet cladding</b>	Sheet steel
<b>Cabinet colour</b>	electrically conductive gray
<b>Base</b>	Classical
<b>Base height approx.</b>	89 mm
<b>Base colour</b>	RAL 7015
<b>Kind of door</b>	Wing door
<b>Door colour</b>	electrically conductive blue
<b>Door handle</b>	Bow handle matt nickel
<b>Lock</b>	Cylinder lock
<b>Locking system</b>	Open
<b>Material of interior fittings</b>	Sheet steel
<b>Bottom tray</b>	Fixed
<b>Bottom tray insert</b>	Grating
<b>Storage levels</b>	1
<b>Storage areas</b>	2
<b>setting height approx.</b>	1177 mm

<b>Number of filling points</b>	1
<b>Load adapter</b>	Yes
<b>Exhaust air monitoring</b>	yes w/display
<b>Ventilation system (w/ventilator)</b>	yes w/enclosure and display
<b>Display</b>	Display, multi-line
<b>Alarm</b>	yes - visual and acoustic
<b>Zusatzausstattung</b>	