

Article Number: 59-30000-098

Product Range Safety equipment

Product Category

black, electrostatically conductive

Dimensions: 365 x 265 x 425 (L x W x H) in mm

with shrink-wrapped sensor support,

e.g. for capacitive level probe (I/O)

black, electrostatically conductive

Dimensions: 365 x 265 x 425 (L x W x H) in mm

with shrink-wrapped sensor support,

e.g. for capacitive level probe (I/O)

HW-category

Safety containers

Outer width approx.

265 mm

Outer depth approx.

365 mm

Outer height approx.

425 mm