

Article Number: 7.00.800

**Product Range** Safety equipment

**Product Category**

Surface hot-dip galvanised according to EN ISO1461

dim in mm: 600 x 860 x 1000 (W x D x H)

Max. load bearing capacity: 350 kg

Surface hot-dip galvanised according to EN ISO1461

dim in mm: 600 x 860 x 1000 (W x D x H)

Max. load bearing capacity: 350 kg

**HW-category**

Transport and Handling

**Outer width approx.**

600 mm

**Outer depth approx.**

860 mm

**Outer height approx.**

1000 mm