

Article Number: 7.00.810

Product Range Safety equipment

Product Category

Surface hot-dip galvanised according to EN ISO1461

dim in mm: 1200 x 860 x 1000 (W x D x H)

Max. load bearing capacity: 700 kg

Surface hot-dip galvanised according to EN ISO1461

dim in mm: 1200 x 860 x 1000 (W x D x H)

Max. load bearing capacity: 700 kg

HW-category

Transport and Handling

Outer width approx.

860 mm

Outer depth approx.

1200 mm

Outer height approx.

1000 mm