

Article Number: 7.02.100

**Product Range** Safety equipment

**Product Category**

Transport of 4 x 10 l or 4 x 20 l canisters:

Conductive collection tray made of PP  
with earthing cable (colour: black),  
watertight welding.

Collection tray insert for guaranteed  
collection volume of max. 22 litres.

Transport trolley with 4 antistatic rollers  
with brakes.

Box for safety goggles.

Stainless steel support for box of disposable  
gloves.

Transport trolley made of powder-coated  
metal, RAL 7015

Dimensions of collection tray (W x D x H) in mm:  
630 x 430 x 325

Collection tray volume in l: 22

Dimensions of the transport trolley (W x D x H)  
in mm: 810 x 445 x 900

Net weight of transport trolley in kg: 30

Transport of 4 x 10 l or 4 x 20 l canisters:

Conductive collection tray made of PP  
with earthing cable (colour: black),  
watertight welding.

Collection tray insert for guaranteed  
collection volume of max. 22 litres.

Transport trolley with 4 antistatic rollers  
with brakes.

Box for safety goggles.

Stainless steel support for box of disposable  
gloves.

Transport trolley made of powder-coated  
metal, RAL 7015

Dimensions of collection tray (W x D x H) in mm:  
630 x 430 x 325

Collection tray volume in l: 22

Dimensions of the transport trolley (W x D x H)

in mm: 810 x 445 x 900

Net weight of transport trolley in kg: 30

<b>HW-category</b>	Transport and Handling
<b>Outer width approx.</b>	810 mm
<b>Outer depth approx.</b>	445 mm
<b>Outer height approx.</b>	900 mm