

Article Number: 7.90.300

Product Range Safety equipment

Product Category

Perforated doors and side walls for natural ventilation.

Sheet steel painted in RAL7035

For max. 8 x 33 kg gas cylinders

Dimensions in mm: 840 x 690 x 1500 (L x W x H)

Turning handle security lock,

locking on 3 sides.

Perforated doors and side walls for natural ventilation.

Sheet steel painted in RAL7035

For max. 8 x 33 kg gas cylinders

Dimensions in mm: 840 x 690 x 1500 (L x W x H)

Turning handle security lock,

locking on 3 sides.

HW-category

Gas cylinder - outside storage

Outer width approx.

690 mm

Outer depth approx.

840 mm

Outer height approx.

1500 mm