

## DEPOT line

Article Number: 70-200740-003

<b>Product Range</b>	Safety storage cabinet
<b>Product Category</b>	Gas cylinder - outside storage

- No safety distance around the gas cylinder depot necessary.
- Good corrosion resistance with polyester powder coating RAL 9002 grey white on galvanised base material.
- Robust construction made of sheet steel, material thickness 1.5 mm (0.6 inch).
- 3-point locking system with door handle with security cylinder lock at an ergonomically favourable height.
- Earthing possibility on the ceiling.
- Chequer plate floor 3 mm (0.12 inch), including corrugation 4.5 mm (1.77 inch).
- For each cylinder rack space, there are 2 penetrations in the ceiling, each Ø 22 mm (0.87 inch), for 13.5 (5,3 inch) PG fittings (closed with plastic plugs).
- 2 horizontal installation rails for mounting fittings.
- One cylinder holder with one retaining belt per standing space.
- Prepared for ground fixing.
- Natural ventilation in accordance with TRGS.
- Labelling with warning symbol W19.
- 

<b>Line</b>	DEPOT
<b>Functionality</b>	Storage
<b>Earthing connection</b>	Yes
<b>Outer width approx.</b>	654 mm
<b>Outer depth approx.</b>	400 mm
<b>Outer height approx.</b>	2053 mm
<b>Max. load bearing capacity per storage area</b>	150 kg
<b>Number of gas cylinder retaining belts</b>	2
<b>Material of cabinet cladding</b>	Sheet steel
<b>Cabinet colour</b>	RAL 9002

<b>Kind of door</b>	Wing door
<b>Door colour</b>	RAL 9002
<b>Door hinge</b>	Right
<b>Door handle</b>	Lever handle black PA
<b>Lock</b>	Cylinder lock
<b>Locking system</b>	Open
<b>Material of interior fittings</b>	Sheet steel
<b>Storage levels</b>	1
<b>Storage areas</b>	1
<b>setting height approx.</b>	1970 mm
<b>Accessories</b>	Yes
<b>Number of inspection windows</b>	1