

DEPOT line

Article Number: 70-201340-003

Product Range Safety storage cabinet
Product Category Gas cylinder - outside storage

- No safety distance around the gas cylinder depot necessary.
- Good corrosion resistance with polyester powder coating RAL 9002 grey white on galvanised base material.
- Robust construction made of sheet steel, material thickness 1.5 mm (0.6 inch).
- 3-point locking system with door handle with security cylinder lock at an ergonomically favourable height.
- Earthing possibility on the ceiling.
- Chequer plate floor 3 mm (0.12 inch), including corrugation 4.5 mm (1.77 inch).
- For each cylinder rack space, there are 2 penetrations in the ceiling, each Ø 22 mm (0.87 inch), for 13.5 (5,3 inch) PG fittings (closed with plastic plugs).
- 2 horizontal installation rails for mounting fittings.
- One cylinder holder with one retaining belt per standing space.
- Prepared for ground fixing.
- Natural ventilation in accordance with TRGS.
- Labelling with warning symbol W19.
-

Line	DEPOT
Functionality	Storage
Earthing connection	Yes
Outer width approx.	1254 mm
Outer depth approx.	400 mm
Outer height approx.	2053 mm
Max. load bearing capacity per storage area	150 kg
Number of gas cylinder retaining belts	4
Material of cabinet cladding	Sheet steel
Cabinet colour	RAL 9002

Kind of door	Wing door
Door colour	RAL 9002
Door handle	Lever handle black PA
Lock	Cylinder lock
Locking system	Open
Material of interior fittings	Sheet steel
Storage levels	1
Storage areas	1
setting height approx.	1970 mm
Zusatzausstattung	
Number of inspection windows	2