

## COOL line

Article Number: 89-200977-041

<b>Product Range</b>	Safety storage cabinet
<b>Product Category</b>	Type 90 - cooled storage

Flammable liquids are cooled and safely stored with the COOL line. Different temperature requirements for flammable liquids can easily be stored in the COOL dual. Here, the temperature can be controlled separately for each of the two cooling compartments between +3 °C (37.4 °F) and +16 °C (60.8 °F).

- **Maximum fire protection**  
Maximum safety with Type 90 technology and cooled interior.
- **Safety**  
In case of fire, a thermocouple automatically initiates the uninterrupted closing of the doors.
- **Working safety**  
Equipotential bonding saddles as a standard on the cabinet help to prevent spark formation.
- **Monitoring with DÜPERTHAL connect**  
Including hardware for monitoring fill level and prepared for online use of monitoring data in the DÜPERTHAL connect app.

<b>Line</b>	COOL
<b>Type</b>	90
<b>Storage type</b>	passive storage
<b>Functionality</b>	Storage
<b>Earthing connection</b>	Yes
<b>Connection socket</b>	Yes
<b>TÜV-Süd certificate type</b>	GS
<b>DIN EN 14470-1</b>	Yes
<b>DIN EN 16121/16122</b>	Yes

<b>Outer width approx.</b>	894 mm
<b>Outer depth approx.</b>	747 mm
<b>Outer height approx.</b>	2045 mm
<b>Max. load bearing capacity per storage area</b>	40 kg
<b>Power supply</b>	230V - 50Hz - IEC 61439
<b>Temperaturprofil</b>	+3°C - +16°C
<b>Connector Type</b>	Type E+F: CEE 7/7
<b>Potential-free contact</b>	Yes
<b>Material of cabinet cladding</b>	Sheet steel
<b>Cabinet colour</b>	RAL 7035
<b>Base</b>	Classical
<b>Base height approx.</b>	89 mm
<b>Base colour</b>	RAL 7015
<b>Kind of door</b>	Wing door
<b>Door colour</b>	RAL 9016
<b>Door hinge</b>	Right
<b>Door handle</b>	Bow handle matt nickel
<b>Lock</b>	Cylinder lock
<b>Locking system</b>	Open
<b>Material of interior fittings</b>	Sheet steel
<b>Bottom tray</b>	Fixed
<b>Bottom tray insert</b>	Perforated sheet insert
<b>Storage shelf</b>	Yes
<b>Storage levels</b>	8
<b>Storage areas</b>	8
<b>setting height approx.</b>	628 mm

<b>Number of penetrations</b>	1
<b>Load adapter</b>	Yes
<b>Exhaust air monitoring</b>	Yes
<b>Zusatzausstattung</b>	